

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

KATALOGNUMMER

34566-284



Combinations of horizontal rails and side panels

+ can be combined - combination not recommended

		Light r.d.	Frontier F	Heavy r.d.	Rugged r.d.
Light r.d.		-	network T1 (standard)	network T2 (standard)	network T3 (standard)
Frontier F		+	network T1 (standard)	network T2 (standard)	network T3 (standard)
Heavy r.d.		+	network T1 (T4)	network T2 (T5)	-
Rugged r.d.		+	network T1 (T4)	network T2 (T5)	-
Side panel					
	Light r.d.	Frontier F	Heavy r.d.	Rugged r.d.	Side panel

+ can be combined - combination not recommended

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICERINGER



FUNKTIONER

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUKTEGENSKABER

Product Type: Horizontal Rail

Produktfamilie: EuropacPRO

Type: Rugged, KD

Rack Width: 84 HP

Length: 431.8 mm

YDERLIGERE PRODUKTOPLYSNINGER

Without M4 thread to front, without printing and without notch for 19" bracket.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE