

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

Power Utilities

Rear horizontal rail for backplane mounting with insulation strip



CERTIFICERINGER



FUNKTIONER

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Dybde	Pakke mængde	For Mounting	Board Depth	Gasket Type
24563-161	3 U	175 mm	1	Backplane	160 mm	Textile
24563-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile
24563-461	6 U	175 mm	1	Backplane	160 mm	Textile
24563-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Håndtag inkluderet	Mounting	Complies With	EMC Shielding	Product Type
24563-161	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-162	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-163	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-164	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-461	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-462	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis
24563-463	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis

Katalognummer	Shock and Vibration Tolerance	Håndtag inkluderet	Mounting	Complies With	EMC Shielding	Product Type
24563-464	5 g (force)	No	Rack	IEC 60297-3-103	No	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Static Load
24563-161	84 HP	15 kgf
24563-162	84 HP	15 kgf
24563-163	84 HP	15 kgf
24563-164	84 HP	15 kgf
24563-461	84 HP	15 kgf
24563-462	84 HP	15 kgf
24563-463	84 HP	15 kgf
24563-464	84 HP	15 kgf

YDERLIGERE PRODUKTOPLYSNINGER

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE