


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded, Front Handle

Power Utilities

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICERINGER



FUNKTIONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded) and includes handles

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

IP 20, in accordance with IEC 60529

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Dybde	Pakke mængde	For Mounting	Board Depth	Shock and Vibration Tolerance
24567-474	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24567-473	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24567-472	6 U	235 mm	1	Backplane	160 mm, 220 mm	5 g (force)
24567-174	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24567-173	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24567-172	3 U	235 mm	1	Backplane	160 mm, 220 mm	5 g (force)

Table 2/3

Katalognummer	Håndtag inkluderet	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24567-474	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis	84 HP
24567-473	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis	84 HP
24567-472	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis	84 HP
24567-174	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis	84 HP
24567-173	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis	84 HP
24567-172	Yes	Rack	IEC 60297-3-103	Yes	Subrack/Chassis	84 HP

Table 3/3

Katalognummer	Static Load
24567-474	15 kgf
24567-473	15 kgf

Katalognummer	Static Load
24567-472	15 kgf
24567-174	15 kgf
24567-173	15 kgf
24567-172	15 kgf

YDERLIGERE PRODUKTOPLYSNINGER

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE