

UFS nVent ERIFLEX Flexibar and IBSB Support Kit

Power Utilities



CERTIFICERINGER



FUNKTIONER

Kit includes one rail and 24 retaining blocks

Create up to three 650 mm (25.6") supports capable of holding four nVent ERIFLEX Flexibar

Retaining blocks are halogen free

RoHS compliant

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Conductor Thickness	Conductor Width	Height (H)	Width (W)	A
UFS-KIT	553590	2 – 8 mm	15.5 – 120.0 mm	57.50 mm	30 mm	24 mm

Table 2/2

Katalognummer	Artikelnummer	B	Unit Weight
UFS-KIT	553590	15 mm	2.300 kg

YDERLIGERE PRODUKTOPLYSNINGER

Recommended distance between supports is 400 mm (15 3/4").

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE