

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Power Utilities

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FUNKTIONER

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Højde	Frame Color	Bredde	Frame Color Code	Cladding Material
10630-034	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Stål
10630-033	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Stål
10630-035	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stål
10630-036	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stål

Table 2/3

Katalognummer	Dybde	Cladding Color	Cladding Color Code	Complies With	Frame Material	Product Type
---------------	-------	----------------	---------------------	---------------	----------------	--------------

10630-034	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stål	Cabinet
10630-033	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stål	Cabinet
10630-035	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stål	Cabinet
10630-036	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Stål	Cabinet

Table 3/3

Katalognummer	Static Load
10630-034	400 kgf
10630-033	400 kgf
10630-035	400 kgf
10630-036	400 kgf

YDERLIGERE PRODUKTOPLYSNINGER

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE