

Varistar CP Steel Door, Glazed With 3-Point Locking, Shortened

Power Utilities

Shortened door available for IP20, IP55 applications.

FEATURES

Glazed door

Height of connection plate 400mm

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Locking Type
21630-342	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-343	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-344	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-345	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-346	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-347	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Catalog Number	Product Type	Protection Rating
21630-342	Cabinet Door	IP20

Catalog Number	Product Type	Protection Rating
21630-343	Cabinet Door	IP20
21630-344	Cabinet Door	IP20
21630-345	Cabinet Door	IP20
21630-346	Cabinet Door	IP20
21630-347	Cabinet Door	IP20

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE