

E650C-G Ground Sensor for Elexant 650c-Modbus



Ground sensor for combined measurement of temperature and moisture values in outdoor areas with foot or vehicle traffic. Robust version made of brass, fully encapsulated. Very low installation height, so particularly well suited to staircases, terraces, etc.

FEATURES

Cable connection: To the side

Connection cable: 4 x 0.5 mm²

Temperature range for moisture measurement: -20°C to 30°C

SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Communication	Diameter	Hazardous Area	Height	IP Rating
1244-022796	E650C-G-HOUSING	No	68 mm	No	31 mm	IP68
1244-022794	E650C-G	No	68 mm	No	72 mm	IP68

Table 2/2

Catalog Number	Item Name	Measuring Range
1244-022796	E650C-G-HOUSING	
1244-022794	E650C-G	-20 to 30 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT