

NGC-40 Series, Power Termination Module



nVent RAYCHEM NGC-40 Series - Power Termination Module accepts a primary and redundant power supply input, also accepts CAN bus inputs and provides for termination of the CAN bus. Each NGC-40-PTM can provide power for a maximum of 10 NGC-40 modules.

FEATURES

Din-rail mounted and part of the NGC-40 system

Provides primary power and CAN bus inputs/termination to the NGC-40 system

Easy to install and reliable

SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Voltage Rating	Voltage Rating Type	Current Rating @ 24 VDC	Operating Temperature	Height
10730-005	NGC-40-PTM	24 V	DC	1.5 A	-40 to 65 °C	87 mm

Table 2/2

Catalog Number	Item Name	Width	Depth
10730-005	NGC-40-PTM	45 mm	106.4 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT