

Protective Grommet



nVent RAYCHEM G-02 is a silicone grommet that protects the heating cable at sharp edges such as endplates of insulation cladding, flanges, etc. It can be cut-to-length and resists temperatures up to 215 °C.

FEATURES

Simple and fast to install

Cut to length, supplied in 1 m pieces

High temperature resistance, up to 215 °C

For use with polymeric heating cables

SPECIFICATIONS

Table 1/1

Catalog Number	Item Name	E-Number	Material	Max Operating Temperature	Length
412549-000	G-02	9935001586	Silicone Rubber	215 °C	1 m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT