

# 19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

## CERTIFICERINGER



## FUNKTIONER

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

## SPECIFIKATIONER

**Product Type:** Assembly Kit

**Finish:** Forzinket Stål

Table 1/2

| Katalognummer | Length | Pakke mængde | Thread Size | Materiale | Produktfamilie | Type |
|---------------|--------|--------------|-------------|-----------|----------------|------|
|---------------|--------|--------------|-------------|-----------|----------------|------|

|           |      |    |    |           |                                                                                                                                                         |                            |
|-----------|------|----|----|-----------|---------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|
| 21190-095 |      | 4  | M6 | Stål, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Eurorack,<br>Outdoor              | Mounting Kit               |
| 21120-196 | 16mm | 4  | M6 | Stål      |                                                                                                                                                         | Mounting Kit,<br>Grounding |
| 21100-435 |      | 8  | M6 | Stål, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack,<br>Outdoor | Mounting Kit               |
| 21120-215 |      | 32 | M6 | Stål      |                                                                                                                                                         | Mounting Kit               |
| 21101-809 |      | 50 | M6 | Stål, ABS | RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Comptec, Inpac,<br>MultipacPRO,<br>Varistar CP,<br>Novastar,<br>Eurorack,<br>Outdoor | Mounting Kit               |
| 21120-214 |      | 50 | M6 | Stål      |                                                                                                                                                         | Mounting Kit               |
| 21120-198 | 16mm | 50 | M6 | Stål      |                                                                                                                                                         | Mounting Kit,<br>Grounding |

|           |      |     |    |           |                                                                                                                           |                         |
|-----------|------|-----|----|-----------|---------------------------------------------------------------------------------------------------------------------------|-------------------------|
| 21101-810 |      | 100 | M6 | Stål, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit            |
| 21120-216 |      | 100 | M6 | Stål      |                                                                                                                           | Mounting Kit            |
| 21120-213 |      | 4   | M6 | Stål      |                                                                                                                           | Mounting Kit            |
| 21120-199 | 13mm | 100 | M6 | Stål      |                                                                                                                           | Mounting Kit, Grounding |
| 21120-197 | 16mm | 32  | M6 | Stål      |                                                                                                                           | Mounting Kit, Grounding |
| 21190-435 |      | 32  | M6 | Stål, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor           | Mounting Kit            |

Table 2/2

| Katalognummer | Works With                                                          | Certificeringer | Hurtigforsendelse |
|---------------|---------------------------------------------------------------------|-----------------|-------------------|
| 21190-095     | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS            | Nej               |
| 21120-196     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 | Nej               |
| 21100-435     | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS            | Nej               |
| 21120-215     | Front Panels, Eurorack, Novastar, Varistar, Varistar CP             |                 | Nej               |

| Katalognummer | Works With                                                                | Certificeringer | Hurtigforsendelse |
|---------------|---------------------------------------------------------------------------|-----------------|-------------------|
| 21101-809     | 19" Cases, 19" Wallmount,<br>19" Indoor Cabinets, 19"<br>Outdoor Cabinets | RoHS            | Nej               |
| 21120-214     | Front Panels, Eurorack,<br>Novastar, Varistar, Varistar<br>CP             |                 | Nej               |
| 21120-198     | Front Panels, Eurorack,<br>Novastar, Varistar, Varistar<br>CP             |                 | Nej               |
| 21101-810     | 19" Cases, 19" Wallmount,<br>19" Indoor Cabinets, 19"<br>Outdoor Cabinets | RoHS            | Nej               |
| 21120-216     | Front Panels, Eurorack,<br>Novastar, Varistar, Varistar<br>CP             |                 | Nej               |
| 21120-213     | Front Panels, Eurorack,<br>Novastar, Varistar, Varistar<br>CP             |                 | Nej               |
| 21120-199     | Front Panels, Eurorack,<br>Novastar, Varistar, Varistar<br>CP             |                 | Nej               |
| 21120-197     | Front Panels, Eurorack,<br>Novastar, Varistar, Varistar<br>CP             |                 | Nej               |
| 21190-435     | 19" Cases, 19" Wallmount,<br>19" Indoor Cabinets, 19"<br>Outdoor Cabinets | RoHS            | Nej               |

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**