

19" Pusher Fan, 2 U, Tangential

Fan tray with tangential pusher fan.



CERTIFICERINGER



FUNKTIONER

2 versions: - LE1: 19" bolt-on dimension, fan unit is wider than 19" - LE2: 19" reduced width, for easy assembly

High air flow

Integrated filter mat

SPECIFIKATIONER

Table 1/1

Katalognummer	Indgangsspænding AC	Pakke mængde	Materiale	Hurtigforsendelse
60713-001	230V	1	Polyamide 66, Polypropylene	Nej
60713-004	115V	1	Polyamide 66, Polypropylene	Nej
60713-003	115V	1	Polyamide 66, Polypropylene	Nej
60713-002	230V	1	Polyamide 66, Polypropylene	Nej

YDERLIGERE PRODUKTOPLYSNINGER

24 VDC on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE