

Basic PDU, EB0xxx, 230 VAC, 1-PH

Modular, compact PDU. Ultra-Low Profile Design



FUNKTIONER

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFIKATIONER

Table 1/6

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	Socket Quantity	Farve
EB0311	Enlogic	Basic PDU	Socket Strip	(12) C13	12	Black
EB0311-A	Enlogic	Basic PDU	Socket Strip	(12) C13	12	Black
EB0317-A	Enlogic	Basic PDU	Socket Strip	(10) C13, (1) C19	11	Black
EB0322	Enlogic	Basic PDU	Socket Strip	(20) C13, (2) C19	22	Black
EB0322-A	Enlogic	Basic PDU	Socket Strip	(30) C13, (6) C19	22	Black
EB0303	Enlogic	Basic PDU	Socket Strip	(6) C19	6	Black
EB0321	Enlogic	Basic PDU	Socket Strip	(20) C13	20	Black
EB0328	Enlogic	Basic PDU	Socket Strip	(24) C13, (6) C19	30	Black

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	SocketQuantity	Farve
EB0332	Enlogic	Basic PDU	Socket Strip	(30) C13, (6) C19	36	Black
EB0337	Enlogic	Basic PDU	Socket Strip	(36) C13, (6) C19	42	Black
EB0318-A	Enlogic	Basic PDU	Socket Strip	(12) C13, (1) C19	13	Black
EB0305	Enlogic	Basic PDU	Socket Strip	(6) C19	6	Black
EB0313	Enlogic	Basic PDU	Socket Strip	(12) C13	12	Black

Table 2/6

Katalognummer	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage
EB0311	No Circuit Breaker	No	0	3.7 kVA	Front Feed	200 – 240V
EB0311-A	16 A, 1-pole, Hy-Mag	No	0		Front Feed	100 – 240V
EB0317-A	16 A, 1-pole, Hy-Mag	No	0		Front Feed	100 – 240V
EB0322	No Circuit Breaker	No	0	3.7 kVA	Top Feed	100 – 240V
EB0322-A	16 A, 1-pole, Hy-Mag	No	0		Front Feed	100 – 240V
EB0303	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Front Feed	200 – 240V
EB0321	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Top Feed	200 – 240V
EB0328	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Top Feed	200 – 240V
EB0332	16 A, 1-pole, Hy-Mag	No	3		Top Feed	200 – 240V
EB0337	16 A, 1-pole, Hy-Mag	No	2	5 kVA North America, 7.4 kVA International	Top Feed	200 – 240V
EB0318-A	16 A, 1-pole, Hy-Mag	No	2		Front Feed	100 – 240V

Katalognummer	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage
EB0305	16 A, 1-pole, Hy-Mag	No	6		Front Feed	200 – 240V
EB0313	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	Front Feed	200 – 240V

Table 3/6

Katalognummer	Phase	Interrupt Rating	Max Power Input	Nominal spænding	On/Off Switch Included	Output Voltage
EB0311	1 PH	5kAIC	3.68 kVA	230V	No	230VAC
EB0311-A	1 PH	5kAIC	3.68 kVA			100 – 240VAC
EB0317-A	1 PH	5kAIC	3.68 kVA			100 – 240VAC
EB0322	1 PH	5kAIC	3.68 kVA	230V	No	230VAC
EB0322-A	1 PH	5kAIC	3.68 kVA			100 – 240VAC
EB0303	1 PH	5kAIC	7.44 kVA	230V	No	230VAC
EB0321	1 PH	5kAIC	7.44 kVA	230V	No	230VAC
EB0328	1 PH	5kAIC	7.44 kVA	230V	No	230VAC
EB0332	1 PH	5kAIC	11.0 kVA			200 – 240VAC
EB0337	1 PH	5kAIC	7.44 kVA	230V	No	230VAC
EB0318-A	1 PH	5kAIC	3.68 kVA			100 – 240VAC
EB0305	1 PH	5kAIC	14.4 kVA			200 – 240VAC
EB0313	1 PH	5kAIC	7.44 kVA	230V	No	230VAC

Table 4/6

Katalognummer	Amperage (Derated Amperage)	Plug Type	Rack Units	Removable Input Cable	Metering Type	Materiale
EB0311	16 A	IEC 60309 316P6 (IP44)	1U	Yes	None	Stål
EB0311-A	16 A	C20	1U	Yes	None	
EB0317-A	20 A (16 A) North America, 16 A International	C20	0U	Yes	None	
EB0322	16 A	IEC 60309 316P6 (IP44)	0U	Yes	None	Stål
EB0322-A	20 A (16 A) North America, 16 A International	C20	0U	Yes	None	
EB0303	32 A	IEC 60309 332P6 (IP44)	0U	No	None	Stål
EB0321	32 A	IEC 60309 332P6 (IP44)	0U	No	None	Stål
EB0328	32 A	IEC 60309 332P6 (IP44)	0U	No	None	Stål
EB0332	63 A	IEC 60309 363P6 (IP44)	0U	No	None	
EB0337	30 A (24 A) North America, 32 A International	IEC 60309 332P6 (IP44)	0U	No	None	Stål
EB0318-A	16 A	C20	2U	Yes	None	
EB0305	63 A	IEC 60309 363P6 (IP44)	1U	No	None	
EB0313	32 A	IEC 60309 332P6 (IP44)	1U	No	None	Stål

Table 5/6

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EB0311	Struktur Pulvermaling	43mm	444mm	41mm	2.25kg	1

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EB0311-A						1
EB0317-A						1
EB0322	Struktur Pulvermaling	817mm	52mm	53mm	3.61kg	1
EB0322-A						1
EB0303	Struktur Pulvermaling	43mm	444mm	197mm		1
EB0321	Struktur Pulvermaling	817mm	52mm	53mm	5.61kg	1
EB0328	Struktur Pulvermaling	1490mm	52mm	53mm	9.5kg	1
EB0332						1
EB0337	Struktur Pulvermaling	1490mm	52mm	53mm	7.21kg	1
EB0318-A						1
EB0305						1
EB0313	Struktur Pulvermaling	43mm	444mm	197mm	5.21kg	1

Table 6/6

Katalognummer	Input Cable Length	Hurtigforsendelse
EB0311	3m	Nej
EB0311-A	0m	Nej
EB0317-A	0m	Nej
EB0322	3m	Nej
EB0322-A	0m	Nej

Katalognummer	Input Cable Length	Hurtigforsendelse
EB0303	3m	Nej
EB0321	3m	Nej
EB0328	3m	Nej
EB0332	3m	Nej
EB0337	3m	Nej
EB0318-A	0m	Nej
EB0305	3m	Nej
EB0313	3m	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, eller anden form for forkert brug af produktet kan resultere i skade på produktet og/eller brand.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE