

Cool Wall Rack White, DCHL-W



nVent Data Solutions Wall-of-Cool Rack er en modulær støttestruktur, der er designet til at implementere og idriftsætte bagdørskølere med fuld kapacitet uden at være afhængig af en bygningsstruktur for stabilitet. The permanent structure allows for networking cabinets to be rolled directly up to rack and secured with a clamp for easy rack-and-roll positioning.

FUNKTIONER

10-gauge ramme i lakeret stål, svejset konstruktion med 12-gauge indvendig flange i lakeret stål.

Simple installation to allow for single person install. Designed to be anchored to the floor for self-sufficiency

Monteringspunkter tilgængelige til understøttelse af køreledningsbane.

Gangable features to support a complete fan wall design for rack and roll deployments.

Integrates directly with standard nVent RDHX Pro without any modificaitons as well as other 3rd party rack manufacturers.

Proven UL stability rated solution to ensure safety.

Kompatibel med top- og bundfremføringsapplikationer med en hævet gulvslangeindtrængning.

Finishen inkluderer RAL9003 (hvid).

SPECIFIKATIONER

Table 1/3

Katalognummer	Product Type	Produktfamilie	Bredde	Dybde	Højde	Beskyttelsesgrad
DWC42U600W	Air/Liquid Heat Exchanger	Cooling	600mm	368mm	2046mm	UL2416
DWC42U750W	Air/Liquid Heat Exchanger	Cooling	750mm	368mm	2046mm	UL2416
DWC42U800W	Air/Liquid Heat Exchanger	Cooling	800mm	368mm	2046mm	UL2416
DWC48U600W	Air/Liquid Heat Exchanger	Cooling	600mm	368mm	2313mm	UL2416
DWC48U750W	Air/Liquid Heat Exchanger	Cooling	750mm	368mm	2313mm	UL2416

Katalognummer	Product Type	Produktfamilie	Bredde	Dybde	Højde	Beskyttelsesgrad
DWC48U800W	Air/Liquid Heat Exchanger	Cooling	800mm	368mm	2313mm	UL2416

Table 2/3

Katalognummer	Materiale	Farve	Farvekode	Finish	Tykkelse	Vægt
DWC42U600W	Lakeret Stål	White	RAL 9003	Struktur Pulvermaling	2.59mm	49.9kg
DWC42U750W	Lakeret Stål	White	RAL 9003	Struktur Pulvermaling	2.59mm	49.9kg
DWC42U800W	Lakeret Stål	White	RAL 9003	Struktur Pulvermaling	2.59mm	40.82kg
DWC48U600W	Lakeret Stål	White	RAL 9003	Struktur Pulvermaling	2.59mm	45.36kg
DWC48U750W	Lakeret Stål	White	RAL 9003	Struktur Pulvermaling	2.59mm	58.97kg
DWC48U800W	Lakeret Stål	White	RAL 9003	Struktur Pulvermaling	2.59mm	54.43kg

Table 3/3

Katalognummer	Hurtigforsendelse
DWC42U600W	Nej
DWC42U750W	Nej
DWC42U800W	Nej
DWC48U600W	Nej
DWC48U750W	Nej
DWC48U800W	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE