

CPCI Serial System With ATX PSU, 4 U, 9 Slot

4 U CompactPCI Serial System with vertical Card Cage for nine 3 U Boards and one built in ATX Power Supply.



CERTIFICERINGER



FUNKTIONER

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG CPCI-S.0

System with vertical card cage. Board format Front: 3 U, 160 mm deep, 9 slot

Backplane 9 slot, 3 U, CompactPCI Serial (single star Ethernet topology)

Heat dissipation via 1 U hot-swap fan unit

ATX power supply, 300 W

SPECIFIKATIONER

Table 1/3

Katalognummer	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
24579-420	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

Katalognummer	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
24579-415	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

Table 2/3

Katalognummer	Indgangsspænding AC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
24579-420	100 – 240V	Bottom to Top	4U	(1) ATX PSU	Yes	Yes
24579-415	100 – 240V	Bottom to Top	4U	(1) ATX PSU	Yes	No

Table 3/3

Katalognummer	Complies With	Dybde	Højde	Pakke mængde	Hurtigforsendelse
24579-420	PICMG CPCI-S.0 R2.0	275mm	177mm	1	Nej
24579-415	PICMG CPCI-S.0 R2.0	275mm	177mm	1	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Modified systems available on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE