

PSU 19" for CompactPCI, AC/DC, 3 U, 300 W

KATALOGNUMMER

13100-143



Pluggable 19" Power Supply with P47 connector, for CompactPCI applications.

FUNKTIONER

Connector P47 and CompactPCI signalling

4 output voltages

Redundant operation with Current Share Bus (CSB), hot-swap

PRODUKTEGENSKABER

Product Type: Power Supply

Type: 19" Switched-Mode

Works With: CompactPCI Systems; VME64x Systems

Indgangsspænding AC: 90 – 264V

Power: 300W

Number of Output Voltages: 4

Voltage 1: 5V

Current 1: 40A

Voltage 2: 3.3V

Current 2: 40A

Voltage 3: 12V

Current 3: 10A

Voltage 4: -12V

Current 4: 2A

Rack Height: 3U

Rack Width: 8HP

Pakke mængde: 1

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE