


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, With Front Handle, 3 U, 175 mm

KATALOGNUMMER

24567-161



Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.

CERTIFICERINGER

FUNKTIONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

PRODUKTEGENSKABER

Rack Height: 3U

Dybde: 175mm

Pakke mængde: 1

For Mounting: Backplane

Board Depth: 160mm

EMC Gasket Type: Stainless Steel

Shock and Vibration Tolerance: 5g (force)

Håndtag inkluderet: Yes

Mounting: Rack

Complies With: IEC 60297-3-103

EMC Shielding: No

Finish: Anodized; Passivated

Materiale: Aluminium

Product Type: Subrack/Chassis

Rack Width: 84HP

Static Load: 15kg

YDERLIGERE PRODUKTOPLYSNINGER

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl,

materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE