

230 Card-Lok

KATALOGNUMMER

W230-2.80TM2



Card Lok designed for PCB retention and thermal transfer within cold wall applications.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

FUNKTIONER

Min expansion 6.99 mm (0.275")

Weight 1.34 g/cm (0.120 oz/")

DSCC 89064 / DSCC CID 59789

Profile 5.59 mm (0.220") x 5.72 mm (0.225")

Flexible mounting options

3 segment, non-shafted design

Length 97 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

For cold wall applications

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

Screw actuated

Average clamp force (4.80", black anodized) = 327 lbs

PRODUKTEGENSKABER

Product Type: PCB Retainer

Materiale: Aluminium

Type: Non-shafted

Thermal Performance: Average

Profile: 5.59 x 5.72 mm

Clamp Force: 136 – 181kgf

Gap Width: PCB + (6.0 - 6.9 mm)

YDERLIGERE PRODUKTOPLYSNINGER

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE