

Etsirack Frame



Welded frame with metric grid holes in accordance with ETS 300119-3, with load capacity of 200 kg.

CERTIFICERINGER



FUNKTIONER

Welded frame with metric grid holes in accordance with ETS 300119-3

Mounting height 81 SU

Static load-carrying capacity 200 kg

Back-to-back row layout is possible

In accordance with standards IEC 48 D and ETS 300 119

Top mounted cabling frame

SPECIFIKATIONER

Static Load:	200kg
Product Type:	Cabinet/Rack Frame
Materiale:	Stål
Frame Material:	Stål

Table 1/2

Katalognummer	Højde	Bredde	Dybde	Pakke mængde	Farve	Farvekode
---------------	-------	--------	-------	--------------	-------	-----------

10125-010	2200mm	600mm	300mm	1	Light Grey	RAL 7035
10125-011	2200mm	600mm	300mm	2	Light Grey	RAL 7035

Table 2/2			
Katalognummer	Finish	Type	Hurtigforsendelse
10125-010	Struktur Pulvermaling	Standard	Nej
10125-011	Struktur Pulvermaling	Standard	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE