

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICERINGER



FUNKTIONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

SPECIFIKATIONER

Materiale: Aluminium

Finish: Anodized; Passivated

EMC Shielding: No
Product Type: Subrack/Chassis

Table 1/3

Katalognummer	Rack Height	Dybde	Pakke mængde	For Mounting	Board Depth	Gasket Type
24567-161	3U	175mm	1	Backplane	160mm	Stainless Steel EMC
24567-162	3U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC
24567-163	3U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC
24567-164	3U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC
24567-461	6U	175mm	1	Backplane	160mm	Stainless Steel EMC
24567-462	6U	235mm	1	Backplane	160mm, 220mm	Stainless Steel EMC
24567-463	6U	295mm	1	Backplane	160mm, 220mm, 280mm	Stainless Steel EMC
24567-464	6U	355mm	1	Backplane	160mm, 220mm, 280mm, 340mm	Stainless Steel EMC

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Håndtag inkluderet	Mounting	Complies With	Rack Width	Static Load
24567-161	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg
24567-162	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg
24567-163	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg
24567-164	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg
24567-461	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg

Katalognummer	Shock and Vibration Tolerance	Håndtag inkluderet	Mounting	Complies With	Rack Width	Static Load
24567-462	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg
24567-463	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg
24567-464	5g (force)	Yes	Rack	IEC 60297-3-103	84HP	15kg

Table 3/3

Katalognummer	Certificeringer	Hurtigforsendelse
24567-161	RoHS	Nej
24567-162	RoHS, DB	Nej
24567-163	DB, RoHS	Nej
24567-164	RoHS, DB	Nej
24567-461	RoHS, DB	Nej
24567-462	DB, RoHS	Nej
24567-463	RoHS, DB	Nej
24567-464	DB, RoHS	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE