

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Non-EMC shielded subrack for backplane mounting, light version.



CERTIFICERINGER



FUNKTIONER

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPECIFIKATIONER

Materiale:	Aluminium
Finish:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis

Table 1/2

Katalognummer	Rack Height	Dybde	Pakke mængde	For Mounting	Board Depth	Håndtag inkluderet
24564-131	3U	175mm	1	Backplane	160mm	No
24564-132	3U	235mm	1	Backplane	160mm, 220mm	No
24564-133	3U	295mm	1	Backplane	160mm, 220mm, 280mm	No
24564-431	6U	175mm	1	Backplane	160mm	No
24564-432	6U	235mm	1	Backplane	160mm, 220mm	No
24564-433	6U	295mm	1	Backplane	160mm, 220mm, 280mm	No

Table 2/2

Katalognummer	Mounting	Complies With	Rack Width	Static Load	Hurtigforsendelse
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Nej
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Nej
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Nej
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Nej
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Nej
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	84HP	7.5kg	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE