

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



CERTIFICERINGER



FUNKTIONER

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

SPECIFIKATIONER

Materiale:	Aluminium
Finish:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis

Table 1/2

Katalognummer	Rack Height	Dybde	Pakke mængde	For Mounting	Board Depth	EMC Gasket Type
24563-191	3U	175mm	1	DIN Connector	160mm	Stainless Steel (retrofittable)
24563-192	3U	235mm	1	DIN Connector	160mm, 220mm	Stainless Steel (retrofittable)
24563-193	3U	295mm	1	DIN Connector	160mm, 220mm, 280mm	Stainless Steel (retrofittable)
24563-194	3U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	Stainless Steel (retrofittable)
24563-491	6U	175mm	1	DIN Connector	160mm	Stainless Steel (retrofittable)
24563-492	6U	235mm	1	DIN Connector	160mm, 220mm	Stainless Steel (retrofittable)
24563-493	6U	295mm	1	DIN Connector	160mm, 220mm, 280mm	Stainless Steel (retrofittable)
24563-494	6U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	Stainless Steel (retrofittable)

Table 2/2

Katalognummer	Håndtag inkluderet	Mounting	Complies With	Rack Width	Static Load	Hurtigforsendelse
24563-191	No	Rack	IEC 60297-3-103	84HP	11kg	Nej
24563-192	No	Rack	IEC 60297-3-103	84HP	11kg	Nej
24563-193	No	Rack	IEC 60297-3-103	84HP	11kg	Nej
24563-194	No	Rack	IEC 60297-3-103	84HP	11kg	Nej
24563-491	No	Rack	IEC 60297-3-103	84HP	11kg	Nej
24563-492	No	Rack	IEC 60297-3-103	84HP	11kg	Nej

Katalognummer	Håndtag inkluderet	Mounting	Complies With	Rack Width	Static Load	Hurtigforsendelse
24563-493	No	Rack	IEC 60297-3-103	84HP	11kg	Nej
24563-494	No	Rack	IEC 60297-3-103	84HP	11kg	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE