

Front Panel, Retrofit Shielding



Flat front panel. Shieldable with stainless steel EMC gasket.

CERTIFICERINGER



FUNKTIONER

For stainless steel EMC gasket

Al, 2.5 mm, front anodized, conductive

SPECIFIKATIONER

Dybde (D):	2.5mm
Materiale:	Aluminium
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)

Table 1/3

Katalognummer	Rack Height	Rack Width	Pakke mængde	Mounting	EMC Gasket Type	Front Finish
20846-424	3U	16HP	1	Screw-on Front	Stainless Steel	Anodized

Katalognummer	Rack Height	Rack Width	Pakke mængde	Mounting	EMC Gasket Type	Front Finish
20846-425	3U	3HP	1	Screw-on Front	Stainless Steel	Anodized
20846-426	3U	4HP	1	Screw-on Front	Stainless Steel	Anodized
20846-427	3U	5HP	1	Screw-on Front	Stainless Steel	Anodized
20846-428	3U	6HP	1	Screw-on Front	Stainless Steel	Anodized
20846-429	3U	7HP	1	Screw-on Front	Stainless Steel	Anodized
20846-430	3U	8HP	1	Screw-on Front	Stainless Steel	Anodized
20846-431	3U	10HP	1	Screw-on Front	Stainless Steel	Anodized
20846-432	3U	12HP	1	Screw-on Front	Stainless Steel	Anodized
20846-433	3U	14HP	1	Screw-on Front	Stainless Steel	Anodized
20846-434	3U	21HP	1	Screw-on Front	Stainless Steel	Anodized
20846-436	3U	28HP	1	Screw-on Front	Stainless Steel	Anodized
20846-437	3U	42HP	1	Screw-on Front	Stainless Steel	Anodized
20846-438	3U	63HP	1	Screw-on Front	Stainless Steel	Anodized
20846-442	6U	3HP	1	Screw-on Front	Stainless Steel	Anodized
20846-443	6U	4HP	1	Screw-on Front	Stainless Steel	Anodized
20846-444	6U	5HP	1	Screw-on Front	Stainless Steel	Anodized
20846-445	6U	6HP	1	Screw-on Front	Stainless Steel	Anodized
20846-446	6U	7HP	1	Screw-on Front	Stainless Steel	Anodized

Katalognummer	Rack Height	Rack Width	Pakke mængde	Mounting	EMC Gasket Type	Front Finish
20846-447	6U	8HP	1	Screw-on Front	Stainless Steel	Anodized
20846-448	6U	10HP	1	Screw-on Front	Stainless Steel	Anodized
20846-449	6U	12HP	1	Screw-on Front	Stainless Steel	Anodized
20846-450	6U	14HP	1	Screw-on Front	Stainless Steel	Anodized
20846-451	6U	21HP	1	Screw-on Front	Stainless Steel	Anodized
20846-452	6U	28HP	1	Screw-on Front	Stainless Steel	Anodized
20846-453	6U	42HP	1	Screw-on Front	Stainless Steel	Anodized
20846-454	6U	63HP	1	Screw-on Front	Stainless Steel	Anodized
20846-456	6U	16HP	1	Screw-on Front	Stainless Steel	Anodized
30846-676	3U	84HP	1	Screw-on Front	Stainless Steel	Anodized
30846-771	6U	84HP	1	Screw-on Front	Stainless Steel	Anodized
30846-588	2U	84HP	1	Screw-on Front	Stainless Steel	Anodized
30846-683	4U	84HP	1	Screw-on Front	Stainless Steel	Anodized
30846-859	9U	84HP	1	Screw-on Front	Stainless Steel	Anodized
30846-864	3U	2HP	1	Screw-on Front	Stainless Steel	Anodized
30846-865	6U	2HP	1	Screw-on Front	Stainless Steel	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Complies With	Finish	Højde (H)	Bredde (W)
---------------	-------------	---------------	---------------	--------	-----------	------------

20846-424	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	80.9mm
20846-425	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	14.9mm
20846-426	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	20mm
20846-427	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	25mm
20846-428	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	30.1mm
20846-429	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	35.2mm
20846-430	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	40.3mm
20846-431	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	50.5mm
20846-432	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	60.6mm
20846-433	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	70.8mm
20846-434	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	106.3mm
20846-436	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	141.9mm
20846-437	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	213mm
20846-438	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	319.7mm
20846-442	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	14.9mm

20846-443	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	20mm
20846-444	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	25mm
20846-445	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	30.1mm
20846-446	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	35.2mm
20846-447	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	40.3mm
20846-448	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	50.5mm
20846-449	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	60.6mm
20846-450	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	70.8mm
20846-451	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	106.3mm
20846-452	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	141.9mm
20846-453	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	213mm
20846-454	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	319.7mm
20846-456	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	80.9mm
30846-676	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized, Passivated	128.4mm	426.4mm
30846-771	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	426.4mm

30846-588	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized, Passivated	84mm	426.4mm
30846-683	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	172.9mm	426.4mm
30846-859	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	395.1mm	426.4mm
30846-864	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	128.4mm	9.8mm
30846-865	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized	261.8mm	9.8mm

Table 3/3

Katalognummer	Hurtigforsendelse
20846-424	Nej
20846-425	Nej
20846-426	Nej
20846-427	Nej
20846-428	Nej
20846-429	Nej
20846-430	Nej
20846-431	Nej
20846-432	Nej
20846-433	Nej
20846-434	Nej


Katalognummer	Hurtigforsendelse
20846-436	Nej
20846-437	Nej
20846-438	Nej
20846-442	Nej
20846-443	Nej
20846-444	Nej
20846-445	Nej
20846-446	Nej
20846-447	Nej
20846-448	Nej
20846-449	Nej
20846-450	Nej
20846-451	Nej
20846-452	Nej
20846-453	Nej
20846-454	Nej
20846-456	Nej
30846-676	Nej

Katalognummer	Hurtigforsendelse
30846-771	Nej
30846-588	Nej
30846-683	Nej
30846-859	Nej
30846-864	Nej
30846-865	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order fixing material (sleeves, collar screws) separately.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE