


# Horizontal Rail Insulation Strip



Strip enables an insulated mounting of backplanes or metal plates as supports for connectors. Creates standardized mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails. Suitable for RatiopacPRO/-AIR, Propac Pro, CompacPRO and EuropacPRO/-Rugged.

## CERTIFICERINGER



## FUNKTIONER

For insulated mounting of backplanes or metal plates as supports for connectors

Creates standardised mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails

## SPECIFIKATIONER

|                        |                                                                       |
|------------------------|-----------------------------------------------------------------------|
| <b>Works With:</b>     | Subracks; Cases                                                       |
| <b>Produktfamilie:</b> | EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac |
| <b>Product Type:</b>   | Insulation Strip                                                      |
| <b>Materiale:</b>      | Polycarbonate                                                         |

Table 1/1

| Katalognummer | Rack Width | Pakke mængde | Flammability Rating | Length  | Hurtigforsendelse |
|---------------|------------|--------------|---------------------|---------|-------------------|
| 24560-820     | 20HP       | 10           | UL® 94V-0           | 101.5mm | Nej               |
| 24560-828     | 28HP       | 10           | UL® 94V-0           | 144.2mm | Nej               |

| Katalognummer | Rack Width | Pakke mængde | Flammability Rating | Length   | Hurtigforsendelse |
|---------------|------------|--------------|---------------------|----------|-------------------|
| 24560-842     | 42HP       | 10           | UL® 94V-0           | 210.4mm  | Nej               |
| 24560-840     | 40HP       | 10           | UL® 94V-0           | 205.12mm | Nej               |
| 24560-863     | 63HP       | 10           | UL® 94V-0           | 316.88mm | Nej               |
| 24560-884     | 84HP       | 10           | UL® 94V-0           | 428.64mm | Nej               |

## YDERLIGERE PRODUKTOPLYSNINGER

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**