

Intelligent PDU, EN2xxx, 230 VAC, 1-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FUNKTIONER

Enlogic EN2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFIKATIONER

Table 1/6

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	Socket Quantity	Farve
EN2316-A	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (4) C19	16	Black
EN2317	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (4) C19	16	Black
EN2326	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN2325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN2329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black
EN2337	Enlogic	Intelligent PDU	Socket Strip	(38) C13, (6) C19	44	Black

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	SocketQuantity	Farve
EN2350	Enlogic	Intelligent PDU	Socket Strip	(20) C13/C15, (20) C13/C15/C19/C 21	40	Black
EN2380	Enlogic	Intelligent PDU	Socket Strip	(16) Locking C13/C15, (16) Locking C13/C15/C19/C 21	32	Black

Table 2/6

Katalognummer	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Length	Input Cable Location
EN2316-A	16 A, 1-pole, Hy-Mag	Yes	0			Front Feed
EN2317	16 A, 1-pole, Hy-Mag	Yes	0			Top Feed
EN2326	No Circuit Breaker	Yes	0	3.7 kVA	3m	Top Feed
EN2325	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed
EN2329	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed
EN2337	16 A, 1-pole, Hy-Mag	Yes	2			Top Feed
EN2350	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed
EN2380	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	3m	Top Feed

Table 3/6

Katalognummer	Input Voltage	Phase	Max Power Input	Nominel spænding	On/Off Switch Included	Output Voltage
EN2316-A	100 – 240V	1 PH	3.68 kVA			100 – 240VAC
EN2317	200 – 240V	1 PH	3.68 kVA			200 – 240VAC
EN2326	100 – 240V	1 PH	3.68 kVA	230V	Yes	230VAC

Katalognummer	Input Voltage	Phase	Max Power Input	Nominal spænding	On/Off Switch Included	Output Voltage
EN2325	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC
EN2329	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC
EN2337	200 – 240V	1 PH	7.44 kVA			200 – 240VAC
EN2350	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC
EN2380	200 – 240V	1 PH	7.44 kVA	230V	Yes	230VAC

Table 4/6

Katalognummer	Amperage (Derated Amperage)	Plug Type	Rack Units	Removable Input Cable	Metering Type	Materiale
EN2316-A	20 A (16 A) North America, 16 A International	C20	0U	Yes	Input	
EN2317	16 A	IEC 60309 316P6 (IP44)	0U	No	Input	
EN2326	16 A	IEC 60309 316P6 (IP44)	0U	Yes	Input	Stål
EN2325	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Stål
EN2329	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Stål
EN2337	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	
EN2350	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Stål
EN2380	32 A	IEC 60309 332P6 (IP44)	0U	No	Input	Stål

Table 5/6

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EN2316-A						1

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EN2317						1
EN2326	Struktur Pulvermaling	1490mm	52mm	53mm	7.21kg	1
EN2325	Struktur Pulvermaling	1750mm	52mm	53mm	9.5kg	1
EN2329	Struktur Pulvermaling	1750mm	52mm	53mm	8.52kg	1
EN2337						1
EN2350	Struktur Pulvermaling	1490mm	56mm	75mm	9.12kg	1
EN2380	Struktur Pulvermaling	1490mm	56mm	75mm		1

Table 6/6

Katalognummer	Interrupt Rating	Hurtigforsendelse
EN2316-A	5kAIC	Nej
EN2317	5kAIC	Nej
EN2326	5kAIC	Nej
EN2325	5kAIC	Nej
EN2329	5kAIC	Nej
EN2337	5kAIC	Nej
EN2350	5kAIC	Nej
EN2380	5kAIC	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE