

Intelligent PDU, EN5xxx, 230 VAC, 1-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FUNKTIONER

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFIKATIONER

Table 1/6

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	Socket Quantity	Farve
EN5403	Enlogic	Intelligent PDU	Socket Strip	(30) C13, (6) C19	36	Black
EN5325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN5329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black
EN5337	Enlogic	Intelligent PDU	Socket Strip	(38) C13, (6) C19	44	Black

Table 2/6

Katalognummer	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Current Rating	Power Rating	Input Cable Location
---------------	-----------------	------------------	--------------------------	----------------	--------------	----------------------

EN5403	16 A, 1-pole, Hy-Mag	No	0			Top Feed
EN5325	16 A, 1-pole, Hy-Mag	No	2		7.4 kVA	Top Feed
EN5329	16 A, 1-pole, Hy-Mag	No	2		7.4 kVA	Top Feed
EN5337	16 A, 1-pole, Hy-Mag	No	2	32A		Top Feed

Table 3/6

Katalognummer	Input Voltage	Phase	Interrupt Rating	Max Power Input	Nominel spænding	On/Off Switch Included
EN5403	400V	3 PH WYE	5kAIC	11.0 kVA		
EN5325	200 – 240V	1 PH	5kAIC	7.44 kVA	230V	No
EN5329	200 – 240V	1 PH	5kAIC	7.44 kVA	230V	No
EN5337	200 – 240V	1 PH	5kAIC	7.44 kVA		

Table 4/6

Katalognummer	Output Voltage	Amperage (Derated Amperage)	Plug Type	Rack Units	Removable Input Cable	Metering Type
EN5403	200 – 240VAC	32 A	IEC 60309 516P6 (IP44)	0U	No	Outlet
EN5325	230VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet
EN5329	230VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet
EN5337	200 – 240VAC	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet

Table 5/6

Katalognummer	Materiale	Finish	Højde	Bredde	Dybde	Vægt
EN5403						
EN5325	Stål	Struktur Pulvermaling	1780mm	52mm	53mm	8.82kg

Katalognummer	Materiale	Finish	Højde	Bredde	Dybde	Vægt
EN5329	Stål	Struktur Pulvermaling	1780mm	52mm	53mm	8.52kg
EN5337						

Table 6/6

Katalognummer	Pakke mængde	Input Cable Length	Hurtigforsendelse
EN5403	1		Nej
EN5325	1	3m	Nej
EN5329	1	3m	Nej
EN5337	1		Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, ...

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE