

Intelligent PDU, EN5xxx, 400 VAC, 3-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FUNKTIONER

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

SPECIFIKATIONER

Table 1/6

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	Socket Quantity	Farve
EN5402	Enlogic	Intelligent PDU	Socket Strip	(18) C13, (6) C19	24	Black
EN5808	Enlogic	Intelligent PDU	Socket Strip	(12) C13, (12) C19	24	Black
EN5810	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (12) C19	36	Black
EN5812	Enlogic	Intelligent PDU	Socket Strip	(36) C13, (12) C19	48	Black
EN5850	Enlogic	Intelligent PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black

Table 2/6

Katalognummer	Switched Outlets	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Input Cable Location	Input Voltage
EN5402	No	No Circuit Breaker	11.0 kVA	0	Top Feed	380 – 415V
EN5808	No	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5810	No	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5812	No	16 A, 1-pole, Hy-Mag		6	Top Feed	400V
EN5850	No	20 A, 1-pole, Hy-Mag	17.3 kVA North America, 22.1 kVA International	6	Top Feed	380 – 415V

Table 3/6

Katalognummer	Phase	Interrupt Rating	Nominal spænding	Max Power Input	On/Off Switch Included	Amperage (Derated Amperage)
EN5402	3 PH		415V	11.0 kVA	No	16 A
EN5808	3 PH		415V	22.0 kVA	No	32 A
EN5810	3 PH		415V	22.0 kVA	No	32 A
EN5812	3 PH WYE	5kAIC		22.0 kVA		32 A
EN5850	3 PH		415V	17.3 / 22.1 kVA	No	30 A (24 A) North America, 32 A International

Table 4/6

Katalognummer	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Materiale
EN5402	230VAC	0U	IEC 60309 516P6 (IP44)	Outlet	No	Stål
EN5808	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	Yes	Stål
EN5810	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	No	Stål

Katalognummer	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Materiale
EN5812	200 – 240VAC	0U	IEC 60309 532P6 (IP44)	Outlet	No	
EN5850	208 – 230VAC	0U	IEC 60309 530P6/532P6	Outlet	No	Stål

Table 5/6

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EN5402	Struktur Pulvermaling	1780mm	52mm	53mm	7.82kg	1
EN5808	Struktur Pulvermaling	1780mm	52mm	53mm		1
EN5810	Struktur Pulvermaling	1780mm	85mm	53mm	12.23kg	1
EN5812						1
EN5850	Struktur Pulvermaling	1780mm	56mm	75mm	11.93kg	1

Table 6/6

Katalognummer	Input Cable Length	Hurtigforsendelse
EN5402	3m	Nej
EN5808	3m	Nej
EN5810	3m	Nej
EN5812		Nej
EN5850	1.8m	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE