

Intelligent PDU, EN6xxx, 230 VAC, 1-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FUNKTIONER

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFIKATIONER

Table 1/6

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	Socket Quantity	Farve
EN6326	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN6325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN6329	Enlogic	Intelligent PDU	Socket Strip	(24) C13, (8) C19	32	Black
EN6337	Enlogic	Intelligent PDU	Socket Strip	(38) C13, (6) C19	44	Black
EN6350	Enlogic	Intelligent PDU	Socket Strip	(20) C13/C15, (20) C13/C15/C19/C21	40	Black

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	SocketQuantity	Farve
EN6380	Enlogic	Intelligent PDU	Socket Strip	(16) Locking C13/C15, (16) Locking C13/C15/C19/C21	32	Black

Table 2/6

Katalognummer	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Location	Input Voltage
EN6326	16 A, 1-pole, Hy-Mag	Yes	0		Top Feed	200 – 240V
EN6325	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V
EN6329	16 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V
EN6337	16 A, 1-pole, Hy-Mag	Yes	2		Top Feed	200 – 240V
EN6350	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V
EN6380	20 A, 1-pole, Hy-Mag	Yes	2	7.4 kVA	Top Feed	200 – 240V

Table 3/6

Katalognummer	Phase	Interrupt Rating	Max Power Input	Nominel spænding	On/Off Switch Included	Output Voltage
EN6326	1 PH	5kAIC	3.68 kVA			200 – 240VAC
EN6325	1 PH	5kAIC	7.44 kVA	230V	Yes	230VAC
EN6329	1 PH	5kAIC	7.44 kVA	230V	Yes	230VAC
EN6337	1 PH	5kAIC	7.44 kVA			200 – 240VAC
EN6350	1 PH	5kAIC	7.44 kVA	230V	Yes	230VAC
EN6380	1 PH	5kAIC	7.44 kVA	230V	Yes	230VAC

Table 4/6

Katalognummer	Amperage (Derated Amperage)	Plug Type	Rack Units	Removable Input Cable	Metering Type	Materiale
EN6326	16 A	IEC 60309 316P6 (IP44)	0U	No	Outlet	
EN6325	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet	Stål
EN6329	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet	Stål
EN6337	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet	
EN6350	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet	Stål
EN6380	32 A	IEC 60309 332P6 (IP44)	0U	No	Outlet	Stål

Table 5/6

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EN6326						1
EN6325	Struktur Pulvermaling	1780mm	52mm	53mm	9kg	1
EN6329	Struktur Pulvermaling	1780mm	52mm	53mm	9.44kg	1
EN6337						1
EN6350	Struktur Pulvermaling	1490mm	56mm	75mm	9.22kg	1
EN6380	Struktur Pulvermaling	1490mm	56mm	75mm		1

Table 6/6

Katalognummer	Input Cable Length	Hurtigforsendelse
EN6326		Nej
EN6325	3m	Nej

Katalognummer	Input Cable Length	Hurtigforsendelse
EN6329	3m	Nej
EN6337		Nej
EN6350	3m	Nej
EN6380	3m	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE