

Interscale Fan Holder With Fans



Interscale Fan Holder With Fans, for desktop cases and 19" chassis. Available in different sizes and with three fan versions, with a air flow volume from 10 to 170 m³/h.

FUNKTIONER

Fan holder for mounting on bottom of case

Fans are simple to fit to the fan holder using vibration-damping fixing material

Fan holders fix into desktop case with 2 plastic feet or into 19" case with 2 screws

Fan holder cannot be used in conjunction with the mounting plate (instead use mounting plate with integrated fan holder)

For technical data of fans, please see delivery includes

SPECIFIKATIONER

Finish: Aluminum-Zinc Plated

Type: Fan Tray

Product Type: Fan Unit

Indgangsspænding DC: 12V min

Table 1/2

Katalognummer	Bredde	Dybde	Pakke mængde	Max Static Pressure	Max Ambient Temperature	Luftstrøm
24828-104	40mm	20mm	1		70°C	10m³/h
24828-105	40mm	20mm	1		70°C	10m³/h
24828-107	40mm	20mm	1		70°C	10m³/h

Katalognummer	Bredde	Dybde	Pakke mængde	Max Static Pressure	Max Ambient Temperature	Luftstrøm
24828-204	80mm	25mm	1		70°C	19m³/h
24828-205	80mm	25mm	1		70°C	19m³/h
24828-207	80mm	25mm	1		70°C	19m³/h
24828-305	119mm	25mm	1		70°C	170m³/h
24828-307	119mm	25mm	1		70°C	170m³/h
24830-101	80mm	25mm	1	95.41Pa	70°C	109m³/h
24830-102	80mm	25mm	1			

Table 2/2						
Katalognummer	Noise Level	Højde	Materiale	Power	Produktfamilie	Hurtigforsendelse
24828-104	18dB(A)	40mm	Stål	0.9W	Interscale	Nej
24828-105	18dB(A)	40mm	Stål	0.9W	Interscale	Nej
24828-107	18dB(A)	40mm	Stål	0.9W	Interscale	Nej
24828-204	32dB(A)	80mm	Stål	2W	Interscale	Nej
24828-205	32dB(A)	80mm	Stål	2W	Interscale	Nej
24828-207	32dB(A)	80mm	Stål	2W	Interscale	Nej
24828-305	43dB(A)	119mm	Stål	5.3W	Interscale	Nej
24828-307	43dB(A)	119mm	Stål	5.3W	Interscale	Nej
24830-101	44.62dB(A)	80mm	Stål			Nej

Katalognummer	Noise Level	Højde	Materiale	Power	Produktfamilie	Hurtigforsendelse
24830-102		80mm	Stål			Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE