

LED Lights for Cabinets



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICERINGER



FUNKTIONER

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

SPECIFIKATIONER

Product Type: Light

Table 1/3

Katalognummer	Indgangsspænding AC	Accessory Type	Indgangsspænding DC	Length	Pakke mængde	Farve
57274	250V max	Lights			1	Black
57275		Lights			2	Black
57265	230V max	Lights	24V max	396mm	1	Black
57272	250V max	Lights		3000mm	1	Black

Katalognummer	Indgangsspænding AC	AccessoryType	Indgangsspænding DC	Length	Pakke mængde	Farve
57273	250V max	Lights		1000mm	1	Black

Table 2/3

Katalognummer	Dybde	Finish	Højde	Materiale	Type	Bredde
57274	14mm	Smooth Matte	53mm	Plastik	Cabinet Light, Terminal Block	18mm
57275	4mm	Smooth Matte	30mm		Cabinet Light, Magnet	12mm
57265	40mm	Smooth Matte		Plastik	Cabinet Light	33mm
57272		Smooth Matte		Plastik	Connection Cable	0.3mm
57273		Smooth Matte		Plastik	Cabinet Light	

Table 3/3

Katalognummer	Farvetemperatur	Nominal spænding	Driftstemperatur	Vægt	Certificeringer	Hurtigforsendelse
57274		250V	60°C min	0.07kg		Nej
57275				0.08kg		Nej
57265	5800K	230V	-20 to 55°C	0.24kg	CE, RoHS	Nej
57272		250V	60°C min			Nej
57273		250V	60°C min	0.3kg		Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE