

Novastar Frame, Slim-Line



Aesthetic aluminum die-cast frame with 200kg static load capacity. Aluminum extruded 19" upright bolted onto the frames.

CERTIFICERINGER



FUNKTIONER

Static load-carrying capacity 200 kg

19" plane - 33 mm at front, 60 mm at rear

Al profile, RAL 7021, incl. grounding

SPECIFIKATIONER

Static Load:	200kg
Frame Material:	Aluminium
Materiale:	Aluminium
Product Type:	Cabinet/Rack Frame

Table 1/2

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
28230-001	6U	323mm	553mm	500mm	1	Black Grey
28230-004	9U	456mm	553mm	500mm	1	Black Grey
28230-007	12U	589mm	553mm	500mm	1	Black Grey
28230-011	16U	767mm	553mm	500mm	1	Black Grey
28230-015	20U	945mm	553mm	500mm	1	Black Grey
28230-020	25U	1167mm	553mm	500mm	1	Black Grey
28230-029	34U	1567mm	553mm	500mm	1	Black Grey
28230-033	38U	1745mm	553mm	500mm	1	Black Grey
28230-042	47U	2145mm	553mm	500mm	1	Black Grey
28230-048	43U	1967mm	553mm	500mm	1	Black Grey
28230-054	12U	589mm	553mm	900mm	1	Black Grey
28230-055	12U	589mm	553mm	1000mm	1	Black Grey
28230-060	6U	323mm	553mm	600mm	1	Black Grey
28230-063	9U	456mm	553mm	600mm	1	Black Grey
28230-066	12U	589mm	553mm	600mm	1	Black Grey
28230-070	16U	767mm	553mm	600mm	1	Black Grey
28230-074	20U	945mm	553mm	600mm	1	Black Grey
28230-079	25U	1167mm	553mm	600mm	1	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
28230-088	34U	1567mm	553mm	600mm	1	Black Grey
28230-092	38U	1745mm	553mm	600mm	1	Black Grey
28230-097	43U	1967mm	553mm	600mm	1	Black Grey
28230-101	47U	2145mm	553mm	600mm	1	Black Grey
28230-126	12U	589mm	553mm	800mm	1	Black Grey
28230-130	16U	767mm	553mm	800mm	1	Black Grey
28230-134	20U	945mm	553mm	800mm	1	Black Grey
28230-139	25U	1167mm	553mm	800mm	1	Black Grey
28230-148	34U	1567mm	553mm	800mm	1	Black Grey
28230-152	38U	1745mm	553mm	800mm	1	Black Grey
28230-157	43U	1967mm	553mm	800mm	1	Black Grey
28230-162	47U	2145mm	553mm	800mm	1	Black Grey
28230-190	16U	767mm	553mm	900mm	1	Black Grey
28230-191	16U	767mm	553mm	1000mm	1	Black Grey
28230-194	20U	945mm	553mm	900mm	1	Black Grey
28230-195	20U	945mm	553mm	1000mm	1	Black Grey
28230-198	25U	1167mm	553mm	900mm	1	Black Grey
28230-199	25U	1167mm	553mm	1000mm	1	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
28230-202	34U	1567mm	553mm	900mm	1	Black Grey
28230-203	34U	1567mm	553mm	1000mm	1	Black Grey
28230-206	38U	1745mm	553mm	900mm	1	Black Grey
28230-207	38U	1745mm	553mm	1000mm	1	Black Grey
28230-210	43U	1967mm	553mm	900mm	1	Black Grey
28230-211	43U	1967mm	553mm	1000mm	1	Black Grey
28230-214	47U	2145mm	553mm	900mm	1	Black Grey
28230-215	47U	2145mm	553mm	1000mm	1	Black Grey
28230-024	29U	1345mm	553mm	500mm	1	Black Grey
28230-083	29U	1345mm	553mm	600mm	1	Black Grey
28230-143	29U	1345mm	553mm	800mm	1	Black Grey
28230-218	29U	1345mm	553mm	1000mm	1	Black Grey
28230-226	29U	1345mm	553mm	900mm	1	Black Grey

Table 2/2

Katalognummer	Farvekode	Finish	Type	Certificeringer	Hurtigforsendelse
28230-001	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-004	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-007	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-011	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej

Katalognummer	Farvekode	Finish	Type	Certificeringer	Hurtigforsendelse
28230-015	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-020	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-029	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-033	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-042	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-048	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-054	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-055	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-060	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-063	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-066	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-070	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-074	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-079	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-088	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-092	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-097	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-101	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej

Katalognummer	Farvekode	Finish	Type	Certificeringer	Hurtigforsendelse
28230-126	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-130	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-134	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-139	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-148	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-152	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-157	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-162	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-190	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-191	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-194	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-195	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-198	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-199	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-202	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-203	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-206	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-207	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej

Katalognummer	Farvekode	Finish	Type	Certificeringer	Hurtigforsendelse
28230-210	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-211	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-214	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-215	RAL 7021	Struktur Pulvermaling	Slim-Line	RoHS	Nej
28230-024	RAL 7021	Struktur Pulvermaling	Slim-Line		Nej
28230-083	RAL 7021	Struktur Pulvermaling	Slim-Line		Nej
28230-143	RAL 7021	Struktur Pulvermaling	Slim-Line		Nej
28230-218	RAL 7021	Struktur Pulvermaling	Slim-Line		Nej
28230-226	RAL 7021	Struktur Pulvermaling	Slim-Line		Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order doors, rear panels, side panels, top cover assemblies, plinths, floors, shelves, slide rails and castors or adjustable feet separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE