

# PropacPRO Portable Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition this case is prepared for the fitting of a tip-up carrying handle, which is part of the extensive accessory range.

## CERTIFICERINGER



## FUNKTIONER

Desktop case for individual assembly

Prepared with holes for fitting of tip-up carrying handle

Retrofitable EMC shielding

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

Prepared for GND/earthing

Conforms with DIN EN 62368-1

## SPECIFIKATIONER

|                        |                                           |
|------------------------|-------------------------------------------|
| <b>Product Type:</b>   | Case                                      |
| <b>Type:</b>           | Case for Individual Electronic Components |
| <b>Produktfamilie:</b> | PropacPRO                                 |

Table 1/3

| Katalognummer | Rack Height | Rack Width | Dybde | Pakke mængde | Usable Height | Usable Width |
|---------------|-------------|------------|-------|--------------|---------------|--------------|
|---------------|-------------|------------|-------|--------------|---------------|--------------|

|           |    |      |       |   |       |       |
|-----------|----|------|-------|---|-------|-------|
| 14577-123 | 3U | 42HP | 326mm | 1 | 130mm | 219mm |
| 14577-125 | 3U | 42HP | 386mm | 1 | 130mm | 219mm |
| 14577-143 | 3U | 63HP | 326mm | 1 | 130mm | 326mm |
| 14577-145 | 3U | 63HP | 386mm | 1 | 130mm | 326mm |
| 14577-163 | 3U | 84HP | 326mm | 1 | 130mm | 432mm |
| 14577-165 | 3U | 84HP | 386mm | 1 | 130mm | 432mm |
| 14577-223 | 4U | 42HP | 326mm | 1 | 174mm | 219mm |
| 14577-243 | 4U | 63HP | 326mm | 1 | 174mm | 326mm |
| 14577-245 | 4U | 63HP | 386mm | 1 | 174mm | 326mm |
| 14577-265 | 4U | 84HP | 386mm | 1 | 174mm | 432mm |

Table 2/3

| Katalognummer | Front Frame Construction | Cooling Option | Complies With   | EMC Shielding      | Finish                            | Højde   |
|---------------|--------------------------|----------------|-----------------|--------------------|-----------------------------------|---------|
| 14577-123     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 155.5mm |
| 14577-125     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 155.5mm |
| 14577-143     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 155.5mm |
| 14577-145     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 155.5mm |
| 14577-163     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 155.5mm |
| 14577-165     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 155.5mm |

| Katalognummer | Front Frame Construction | Cooling Option | Complies With   | EMC Shielding      | Finish                            | Højde |
|---------------|--------------------------|----------------|-----------------|--------------------|-----------------------------------|-------|
| 14577-223     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 200mm |
| 14577-243     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 200mm |
| 14577-245     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 200mm |
| 14577-265     | Single Piece             | No             | IEC 60297-3-101 | No (Retrofittable) | Passivated, Struktur Pulvermaling | 200mm |

Table 3/3

| Katalognummer | Materiale | Beskyttelsesgrad | Static Load | Bredde  | Hurtigforsendelse |
|---------------|-----------|------------------|-------------|---------|-------------------|
| 14577-123     | Aluminium | IP20             | 25kg        | 257mm   | Nej               |
| 14577-125     | Aluminium | IP20             | 25kg        | 257mm   | Nej               |
| 14577-143     | Aluminium | IP20             | 25kg        | 363.7mm | Nej               |
| 14577-145     | Aluminium | IP20             | 25kg        | 363.7mm | Nej               |
| 14577-163     | Aluminium | IP20             | 25kg        | 470.3mm | Nej               |
| 14577-165     | Aluminium | IP20             | 25kg        | 470.3mm | Nej               |
| 14577-223     | Aluminium | IP20             | 25kg        | 257mm   | Nej               |
| 14577-243     | Aluminium | IP20             | 25kg        | 363.7mm | Nej               |
| 14577-245     | Aluminium | IP20             | 25kg        | 363.7mm | Nej               |
| 14577-265     | Aluminium | IP20             | 25kg        | 470.3mm | Nej               |

## YDERLIGERE PRODUKTOPLYSNINGER

Please order tip up carrying handle separatly.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**