

# PSU 19" AC/DC Linear Regulator, Dual

Linear regulator for application which only allows a very low noise level at the outputs.



## CERTIFICERINGER



## FUNKTIONER

2 output voltages, galvanically separated

High control accuracy, low residual ripple and very low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

## SPECIFIKATIONER

Table 1/3

| Katalognummer | Type                 | Indgangsspænding AC | Power | Number of Output Voltages | Voltage 1 | Current 1 |
|---------------|----------------------|---------------------|-------|---------------------------|-----------|-----------|
| 13105-017     | 19" Linear Regulator | 230V                | 10W   | 2                         | 12V       | 0.4A      |
| 13105-018     | 19" Linear Regulator | 230V                | 12W   | 2                         | 15V       | 0.4A      |
| 13105-022     | 19" Linear Regulator | 230V                | 24W   | 2                         | 12V       | 1A        |

| Katalognummer | Type                 | Indgangsspænding AC | Power | Number of Output Voltages | Voltage 1 | Current 1 |
|---------------|----------------------|---------------------|-------|---------------------------|-----------|-----------|
| 13105-023     | 19" Linear Regulator | 230V                | 30W   | 2                         | 15V       | 1A        |
| 13105-021     | 19" Linear Regulator | 230V                | 14W   | 2                         | 5V        | 1.4A      |
| 13105-027     | 19" Linear Regulator | 230V                | 36W   | 2                         | 12V       | 1.5A      |
| 13105-028     | 19" Linear Regulator | 230V                | 45W   | 2                         | 15V       | 1.5A      |
| 13105-029     | 19" Linear Regulator | 230V                | 58W   | 2                         | 24V       | 1.2A      |

Table 2/3

| Katalognummer | Voltage 2 | Current 2 | Rack Height | Rack Width | Dybde    | Pakke mængde |
|---------------|-----------|-----------|-------------|------------|----------|--------------|
| 13105-017     | 12V       | 0.4A      | 3U          | 6HP        | 171.93mm | 1            |
| 13105-018     | 15V       | 0.4A      | 3U          | 6HP        | 171.93mm | 1            |
| 13105-022     | 12V       | 1A        | 3U          | 10HP       | 171.93mm | 1            |
| 13105-023     | 15V       | 1A        | 3U          | 10HP       | 171.93mm | 1            |
| 13105-021     | 5V        | 1.4A      | 3U          | 10HP       | 171.93mm | 1            |
| 13105-027     | 12V       | 1.5A      | 3U          | 14HP       | 171.93mm | 1            |
| 13105-028     | 15V       | 1.5A      | 3U          | 14HP       | 171.93mm | 1            |
| 13105-029     | 24V       | 1.2A      | 3U          | 14HP       | 171.93mm | 1            |

Table 3/3

| Katalognummer | Certificeringer      | Hurtigforsendelse |
|---------------|----------------------|-------------------|
| 13105-017     | RoHS, CE, EN 62368-1 | Nej               |
| 13105-018     | CE, EN 62368-1, RoHS | Nej               |

| Katalognummer | Certificeringer | Hurtigforsendelse |
|---------------|-----------------|-------------------|
| 13105-022     | CE, RoHS        | Nej               |
| 13105-023     | RoHS, CE        | Nej               |
| 13105-021     | RoHS, CE        | Nej               |
| 13105-027     | CE, RoHS        | Nej               |
| 13105-028     | RoHS, CE        | Nej               |
| 13105-029     | CE, RoHS        | Nej               |

## YDERLIGERE PRODUKTOPLYSNINGER

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**