

PSU 19" AC/DC, Maxpower 100 W, Dual



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and two output voltages.

CERTIFICERINGER



FUNKTIONER

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active power-factor correction (PFC)

2 output voltages

High power density

Efficiency up to 80 %

SPECIFIKATIONER

Table 1/3

Katalognummer	Type	Indgangsspænding AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-116	19" Switched-Mode	90 – 264V	102W	2	15V	3.4A
13100-115	19" Switched-Mode	90 – 264V	101W	2	12V	4.2A
13100-114	19" Switched-Mode	90 – 264V	93W	2	5V	9A

Katalognummer	Type	Indgangsspænding AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-112	19" Switched-Mode	90 – 264V	93W	2	5V	9A

Table 2/3

Katalognummer	Voltage 2	Current 2	Rack Height	Rack Width	Dybde	Pakke mængde
13100-116	15V	3.4A	3U	8HP	171.93mm	1
13100-115	12V	4.2A	3U	8HP	171.93mm	1
13100-114	24V	2A	3U	8HP	171.93mm	1
13100-112	12V	4A	3U	8HP	171.93mm	1

Table 3/3

Katalognummer	Certificeringer	Hurtigforsendelse
13100-116	RoHS, CE, UR	Nej
13100-115	CE, UR, RoHS	Nej
13100-114	RoHS, CE, UR	Nej
13100-112	CE, CSA, RoHS	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order front panel separately.

Output data at mains voltage > 190 VAC, Ta = 0 ... 50 °C.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE