

# PSU 19" AC/DC Maxpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

## CERTIFICERINGER



## FUNKTIONER

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active power factor correction (PFC)

1 output voltage

Signalling: Output voltage OK

High power density

Integrated decoupling diode for redundancy operation

Active Current Share Bus (CSB)

## SPECIFIKATIONER

Table 1/2

| Katalognummer | Type              | Indgangsspænding AC | Power | Number of Output Voltages | Voltage 1 | Current 1 |
|---------------|-------------------|---------------------|-------|---------------------------|-----------|-----------|
| 13100-104     | 19" Switched-Mode | 90 – 264V           | 99W   | 1                         | 15V       | 6.6A      |
| 13100-103     | 19" Switched-Mode | 90 – 264V           | 100W  | 1                         | 12V       | 8.3A      |

| Katalognummer | Type              | Indgangsspænding AC | Power | Number of Output Voltages | Voltage 1 | Current 1 |
|---------------|-------------------|---------------------|-------|---------------------------|-----------|-----------|
| 13100-102     | 19" Switched-Mode | 90 – 264V           | 80W   | 1                         | 5V        | 16A       |
| 13100-105     | 19" Switched-Mode | 90 – 264V           | 101W  | 1                         | 24V       | 4.2A      |

Table 2/2

| Katalognummer | Rack Height | Rack Width | Pakke mængde | Hurtigforsendelse |
|---------------|-------------|------------|--------------|-------------------|
| 13100-104     | 3U          | 6HP        | 1            | Nej               |
| 13100-103     | 3U          | 6HP        | 1            | Nej               |
| 13100-102     | 3U          | 6HP        | 1            | Nej               |
| 13100-105     | 3U          | 6HP        | 1            | Nej               |

## YDERLIGERE PRODUKTOPLYSNINGER

Please order front panel separately.

Output data at mains voltage > 190 VAC, Ta = 0 ...50 °C.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**