

PSU 19" DC/DC Coolpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications.

CERTIFICERINGER



FUNKTIONER

Wide input voltage range from 20 to 72 VDC

Galvanic separation between primary and secondary circuits

High power density

External ON/OFF

SPECIFIKATIONER

Table 1/2

Katalognummer	Type	Indgangsspænding DC	Power	Number of Output Voltages	Voltage 1	Current 1
13103-003	19" DC/DC Converter	20 – 72V	102W	1	12V	8.5A
13103-004	19" DC/DC Converter	20 – 72V	100W	1	15V	6.7A
13103-002	19" DC/DC Converter	20 – 72V	100W	1	5V	20A

Table 2/2

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Hurtigforsendelse
13103-003	3U	6HP	171.93mm	1	Nej
13103-004	3U	6HP	171.93mm	1	Nej
13103-002	3U	6HP	171.93mm	1	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order front panel separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE