


RackChiller In-Row 45 Height Adapter



The RackChiller In-Row 45 Height Adaptor allows for integration of the cooler into aisle containments of racks higher than 42RU. The top blanking panel assures seamless look while providing best sealing properties of the aisle containment. The kit is available in different heights.

FUNKTIONER

Adapts the RackChiller In-Row 45 into aisle containments with racks of 47RU or 52RU

SPECIFIKATIONER

Table 1/1

Katalognummer	Finish	Materiale	Pakke mængde	Rack Height	Bredde	Hurtigforsendelse
24630-189	Struktur Pulvermaling	Stål	1	47U	300mm	Nej
24630-190	Struktur Pulvermaling	Stål	1	52U	300mm	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Not to be used in combination with a base plinth

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE