

RatiopacPRO/-AIR Strap Handle



Strap handle for RatiopacPRO/-AIR with a static load-carrying capacity of 20 kg. Retrofittable without mechanical tooling on case.

CERTIFICERINGER



FUNKTIONER

Static load-carrying capacity 20 kg

Retrofittable without mechanical tooling on the case side panel

SPECIFIKATIONER

- Works With:** Cases
- Product Type:** Handle
- Produktfamilie:** RatiopacPRO; RatiopacPRO AIR

Table 1/1

Katalognummer	Rack Height	Dybde	Pakke mængde	Håndtagstype	Hurtigforsendelse
24571-308	3U	315mm	1	Strap	Nej
24571-316	4U	435mm	1	Strap	Nej
24571-315	4U	375mm	1	Strap	Nej
24571-314	4U	315mm	1	Strap	Nej

Katalognummer	Rack Height	Dybde	Pakke mængde	Håndtagstype	Hurtigforsendelse
24571-309	3U	375mm	1	Strap	Nej
24571-310	3U	435mm	1	Strap	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE