

Secure Dual W-Lock Power Cord



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

FUNKTIONER

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

SPECIFIKATIONER

Table 1/2

Katalognummer	Type	Works With	Length	Farve	Højde	Input Cable Length
EP1314024X150	Cable	RackPower	600mm	Black	270mm	588m
EP1314048X125	Cable	RackPower	1200mm	Black	270mm	1.176m
EP1314072X100	Cable	RackPower	1800mm	Black	270mm	1.764m
EP1314B24X150	Cable	RackPower	600mm	Blue	270mm	0.588m
EP1314B48X125	Cable	RackPower	1200mm	Blue	270mm	1.176m

Katalognummer	Type	Works With	Length	Farve	Højde	Input Cable Length
EP1314B72X100	Cable	RackPower	1800mm	Blue	270mm	1.764m
EP1314R24X150	Cable	RackPower	600mm	Red	270mm	0.588m
EP1314R48X125	Cable	RackPower	1200mm	Red	270mm	1.176m
EP1314R72X100	Cable	RackPower	1800mm	Red	270mm	1.764m
EP1920024X100	Cable	RackPower	600mm	Black	270mm	0.588m
EP1920048X75	Cable	RackPower	1200mm	Black	270mm	1.176m
EP1920072X50	Cable	RackPower	1800mm	Black	270mm	1.764m
EP1920B24X100	Cable	RackPower	600mm	Blue	270mm	0.588m
EP1920B48X75	Cable	RackPower	1200mm	Blue	270mm	1.176m
EP1920B72X50	Cable	RackPower	1800mm	Blue	270mm	1.764m
EP1920R24X100	Cable	RackPower	600mm	Red	270mm	0.588m
EP1920R48X75	Cable	RackPower	1200mm	Red	270mm	1.176m
EP1920R72X50	Cable	RackPower	1800mm	Red	270mm	1.764m

Table 2/2

Katalognummer	Pakke mængde	Plug Type	Removable Input Cable	Hurtigforsendelse
EP1314024X150	150	C13/C14	No	Nej

Katalognummer	Pakke mængde	Plug Type	Removable InputCable	Hurtigforsendelse
EP1314048X125	125	C13/C14	No	Nej
EP1314072X100	100	C13/C14	No	Nej
EP1314B24X150	150	C13/C14	No	Nej
EP1314B48X125	125	C13/C14	No	Nej
EP1314B72X100	100	C13/C14	No	Nej
EP1314R24X150	150	C13/C14	No	Nej
EP1314R48X125	125	C13/C14	No	Nej
EP1314R72X100	100	C13/C14	No	Nej
EP1920024X100	100	C19/C20	No	Nej
EP1920048X75	75	C19/C20	No	Nej
EP1920072X50	50	C19/C20	No	Nej
EP1920B24X100	100	C19/C20	No	Nej
EP1920B48X75	75	C19/C20	No	Nej
EP1920B72X50	50	C19/C20	No	Nej
EP1920R24X100	100	C19/C20	No	Nej
EP1920R48X75	75	C19/C20	No	Nej
EP1920R72X50	50	C19/C20	No	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE