

Socket Strip, IEC C13, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICERINGER



FUNKTIONER

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPECIFIKATIONER

Length:	438.5mm
Materiale:	Aluminium; Polyamide
Product Type:	Socket Strip

Table 1/2

Katalognummer	Stiktype	Socket Quantity	Switched Outlets	Spænding AC	Function	Pakke mængde
60110-340	IEC C13	12	No	230V		1

Katalognummer	Stiktype	SocketQuantity	Switched Outlets	Spænding AC	Function	Pakke mængde
60110-341	IEC C13	12	No	230V		1
60110-342	IEC C13	12	No	230V		1
60110-349	IEC C13	6	No	230V	Overcurrent Protection	1
60110-350	IEC C13	6	No	230V	Overcurrent Protection	1
60110-351	IEC C13	6	No	230V	Overcurrent Protection	1

Table 2/2

Katalognummer	Farve	Dybde	Finish	Hurtigforsendelse
60110-340	Grey	44mm	Anodized	Nej
60110-341	Black	44mm	Anodized	Nej
60110-342	Red	44mm	Anodized	Nej
60110-349	Grey	44mm	Anodized	Nej
60110-350	Black	44mm	Anodized	Nej
60110-351	Red	44mm	Anodized	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order mounting bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE