

# Socket Strip, UTE, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

## CERTIFICERINGER



## FUNKTIONER

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during fitting

Output via UTE sockets

Horizontal or vertical mounting

Installation height 1 U

In accordance with NFC 61-303

## SPECIFIKATIONER

|                      |                      |
|----------------------|----------------------|
| <b>Length:</b>       | 438.5mm              |
| <b>Materiale:</b>    | Aluminium; Polyamide |
| <b>Product Type:</b> | Socket Strip         |

Table 1/2

| Katalognummer | Stiktype | Socket Quantity | Switched Outlets | Spænding AC | Function               | Pakke mængde |
|---------------|----------|-----------------|------------------|-------------|------------------------|--------------|
| 60110-357     | UTE      | 6               | No               | 230V        | Overcurrent Protection | 1            |

| Katalognummer | Stiktype | SocketQuantity | Switched Outlets | Spænding AC | Function               | Pakke mængde |
|---------------|----------|----------------|------------------|-------------|------------------------|--------------|
| 60110-356     | UTE      | 6              | No               | 230V        | Overcurrent Protection | 1            |
| 60110-346     | UTE      | 8              | No               | 230V        |                        | 1            |
| 60110-355     | UTE      | 6              | No               | 230V        | Overcurrent Protection | 1            |
| 60110-348     | UTE      | 8              | No               | 230V        |                        | 1            |
| 60110-347     | UTE      | 8              | No               | 230V        |                        | 1            |

Table 2/2

| Katalognummer | Farve | Dybde | Finish   | Hurtigforsendelse |
|---------------|-------|-------|----------|-------------------|
| 60110-357     | Red   | 44mm  | Anodized | Nej               |
| 60110-356     | Black | 44mm  | Anodized | Nej               |
| 60110-346     | White | 44mm  | Anodized | Nej               |
| 60110-355     | White | 44mm  | Anodized | Nej               |
| 60110-348     | Red   | 44mm  | Anodized | Nej               |
| 60110-347     | Black | 44mm  | Anodized | Nej               |

## YDERLIGERE PRODUKTOPLYSNINGER

Please order mounting bracket for vertical mounting separately.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**