

Varistar CP Cabinet Frame, Seismic Heavy Load



Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FUNKTIONER

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded heavy-duty frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 500 kg to IEC 61587-2

SPECIFIKATIONER

Dynamic Load:	500kg
Static Load:	1600kg
Product Type:	Cabinet/Rack Frame
Frame Material:	Stål

Table 1/3

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Shock and Vibration Tolerance
20630-273	33U	1600mm	600mm	600mm	1	5g (force)
20630-274	33U	1600mm	600mm	800mm	1	5g (force)
20630-275	33U	1600mm	800mm	600mm	1	5g (force)
20630-276	33U	1600mm	800mm	800mm	1	5g (force)

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Shock and Vibration Tolerance
20630-277	38U	1800mm	600mm	600mm	1	5g (force)
20630-278	38U	1800mm	800mm	600mm	1	5g (force)
20630-279	38U	1800mm	800mm	600mm	1	5g (force)
20630-280	38U	1800mm	800mm	800mm	1	5g (force)
20630-281	42U	2000mm	600mm	600mm	1	5g (force)
20630-282	42U	2000mm	600mm	800mm	1	5g (force)
20630-283	42U	2000mm	800mm	600mm	1	5g (force)
20630-284	42U	2000mm	800mm	1600mm	1	5g (force)
20630-285	42U	2200mm	600mm	600mm	1	5g (force)
20630-286	47U	2200mm	600mm	800mm	1	5g (force)
20630-287	47U	2200mm	800mm	600mm	1	5g (force)
20630-288	47U	2200mm	800mm	800mm	1	5g (force)
20630-269	42U	2000mm	600mm	1000mm	1	5g (force)
20630-270	42U	2000mm	600mm	1200mm	1	5g (force)
20630-271	42U	2000mm	800mm	1000mm	1	5g (force)
20630-272	42U	2000mm	800mm	1200mm	1	5g (force)

Table 2/3

Katalognummer	Frequency	Farve	Farvekode	Complies With	Finish	Materiale
---------------	-----------	-------	-----------	---------------	--------	-----------

20630-273	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-274	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-275	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-276	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-277	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-278	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-279	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-280	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-281	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-282	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-283	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-284	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-285	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-286	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-287	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-288	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-269	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-270	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
20630-271	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål

20630-272	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Struktur Pulvermaling	Stål
-----------	-------	------------	----------	-----------------------------	--------------------------	------

Table 3/3

Katalognummer	Type	Works With	Hurtigforsendelse
20630-273	Heavy Load	Varistar CP	Nej
20630-274	Heavy Load	Varistar CP	Nej
20630-275	Heavy Load	Varistar CP	Nej
20630-276	Heavy Load	Varistar CP	Nej
20630-277	Heavy Load	Varistar CP	Nej
20630-278	Heavy Load	Varistar CP	Nej
20630-279	Heavy Load	Varistar CP	Nej
20630-280	Heavy Load	Varistar CP	Nej
20630-281	Heavy Load	Varistar CP	Nej
20630-282	Heavy Load	Varistar CP	Nej
20630-283	Heavy Load	Varistar CP	Nej
20630-284	Heavy Load	Varistar CP	Nej
20630-285	Heavy Load	Varistar CP	Nej
20630-286	Heavy Load	Varistar CP	Nej
20630-287	Heavy Load	Varistar CP	Nej
20630-288	Heavy Load	Varistar CP	Nej
20630-269	Heavy Load	Varistar CP	Nej

Katalognummer	Type	Works With	Hurtigforsendelse
20630-270	Heavy Load		Nej
20630-271	Heavy Load	Varistar CP	Nej
20630-272	Heavy Load	Varistar CP	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please order attachments and components separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE