

Varistar CP Side Panel, Divided, With Quick-Release Fastener and Lock



Side panels (2 pieces) with Quick-Release Fastener without grounding kit for Varistar CP cabinets.

FUNKTIONER

Steel, 1 mm

2 splitted Side panel without grounding kit

Safety lock kit included

SPECIFIKATIONER

Product Type: Cabinet/Rack Panel

Beskyttelsesgrad: IP20

Table 1/2

Katalognummer	Rack Height	Højde	Dybde	Pakke mængde	Farve	Farvekode
21630-061	42U	2000mm	1000mm	2	Black Grey	RAL 7021
21630-062	42U	2000mm	1100mm	2	Black Grey	RAL 7021
21630-063	42U	2000mm	1200mm	2	Black Grey	RAL 7021
21630-067	47U	2200mm	1000mm	2	Black Grey	RAL 7021
21630-068	47U	2200mm	1100mm	2	Black Grey	RAL 7021

Katalognummer	Rack Height	Højde	Dybde	Pakke mængde	Farve	Farvekode
21630-069	47U	2200mm	1200mm	2	Black Grey	RAL 7021
21630-073	52U	2450mm	1000mm	2	Black Grey	RAL 7021
21630-074	52U	2450mm	1100mm	2	Black Grey	RAL 7021
21630-075	52U	2450mm	1200mm	2	Black Grey	RAL 7021

Table 2/2

Katalognummer	Finish	Materiale	Type	Hurtigforsendelse
21630-061	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-062	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-063	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-067	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-068	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-069	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-073	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-074	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-075	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl,

materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE