

Varistar CP Side Panel With Quick-Release Fastener and Lock

Varistar Side Panels with Quick-Release Fastener without grounding kit.



FUNKTIONER

Steel, 1 mm

Side panel without grounding kit

Safety lock kit included

SPECIFIKATIONER

Product Type: Cabinet/Rack Panel

Beskyttelsesgrad: IP20

Table 1/2

Katalognummer	Rack Height	Højde	Dybde	Pakke mængde	Farve	Farvekode
21630-285	24U	1200mm	600mm	2	Black Grey	RAL 7021
21630-286	24U	1200mm	800mm	2	Black Grey	RAL 7021
21630-289	29U	1400mm	600mm	2	Black Grey	RAL 7021
21630-290	29U	1400mm	800mm	2	Black Grey	RAL 7021
21630-293	33U	1600mm	600mm	2	Black Grey	RAL 7021

Katalognummer	Rack Height	Højde	Dybde	Pakke mængde	Farve	Farvekode
21630-294	33U	1600mm	800mm	2	Black Grey	RAL 7021
21630-297	38U	1800mm	600mm	2	Black Grey	RAL 7021
21630-298	38U	1800mm	800mm	2	Black Grey	RAL 7021
21630-302	42U	2000mm	600mm	2	Black Grey	RAL 7021
21630-303	42U	2000mm	800mm	2	Black Grey	RAL 7021
21630-304	42U	2000mm	900mm	2	Black Grey	RAL 7021
21630-064	42U	2000mm	1000mm	2	Black Grey	RAL 7021
21630-306	47U	2200mm	600mm	2	Black Grey	RAL 7021
21630-307	47U	2200mm	800mm	2	Black Grey	RAL 7021
21630-308	47U	2200mm	900mm	2	Black Grey	RAL 7021
21630-070	47U	2200mm	1000mm	2	Black Grey	RAL 7021
21630-287	24U	1200mm	900mm	2	Black Grey	RAL 7021
21630-288	24U	1200mm	1000mm	2	Black Grey	RAL 7021
21630-291	29U	1400mm	900mm	2	Black Grey	RAL 7021
21630-292	29U	1400mm	1000mm	2	Black Grey	RAL 7021
21630-295	33U	1600mm	900mm	2	Black Grey	RAL 7021
21630-296	33U	1600mm	1000mm	2	Black Grey	RAL 7021
21630-299	38U	1800mm	900mm	2	Black Grey	RAL 7021

Katalognummer	Rack Height	Højde	Dybde	Pakke mængde	Farve	Farvekode
21630-300	38U	1800mm	1000mm	2	Black Grey	RAL 7021
21630-065	42U	2000mm	1100mm	2	Black Grey	RAL 7021
21630-066	42U	2000mm	1200mm	2	Black Grey	RAL 7021
21630-071	47U	2200mm	1100mm	2	Black Grey	RAL 7021
21630-072	47U	2200mm	1200mm	2	Black Grey	RAL 7021

Table 2/2

Katalognummer	Finish	Materiale	Type	Hurtigforsendelse
21630-285	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-286	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-289	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-290	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-293	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-294	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-297	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-298	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-302	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-303	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-304	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-064	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej

Katalognummer	Finish	Materiale	Type	Hurtigforsendelse
21630-306	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-307	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-308	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-070	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-287	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-288	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-291	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-292	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-295	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-296	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-299	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-300	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-065	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-066	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-071	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej
21630-072	Struktur Pulvermaling	Stål	Side Panel, Quick Release	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE