

Varistar CP Steel Door, Plain, Multi-Point Locking

EMC and IP55 Steel Door with lever handle and 4-Point locking.

FUNKTIONER

Lever handle with push button

Opening angle 180°

Steel door with 4-point locking for EMC applications

SPECIFIKATIONER

Product Type: Cabinet Door
Beskyttelsesgrad: IP55
Materiale: Stainless Steel

Table 1/2

Katalognummer	Rack Height	Højde	Bredde	Pakke mængde	Finish	Locking Type
21630-521	24U	1200mm	600mm	1	Struktur Pulvermaling	3-Point Locking
21630-522	24U	1200mm	800mm	1	Struktur Pulvermaling	3-Point Locking
21630-523	29U	1400mm	600mm	1	Struktur Pulvermaling	3-Point Locking
21630-524	29U	1400mm	800mm	1	Struktur Pulvermaling	3-Point Locking
21630-525	33U	1600mm	600mm	1	Struktur Pulvermaling	4-Point Locking
21630-526	33U	1600mm	800mm	1	Struktur Pulvermaling	4-Point Locking
21630-527	38U	1800mm	600mm	1	Struktur Pulvermaling	4-Point Locking

Katalognummer	Rack Height	Højde	Bredde	Pakke mængde	Finish	Locking Type
21630-528	38U	1800mm	800mm	1	Struktur Pulvermaling	4-Point Locking
21630-529	42U	2000mm	600mm	1	Struktur Pulvermaling	4-Point Locking
21630-530	42U	2000mm	800mm	1	Struktur Pulvermaling	4-Point Locking
21630-531	47U	2200mm	600mm	1	Struktur Pulvermaling	5-Point Locking
21630-532	47U	2200mm	800mm	1	Struktur Pulvermaling	5-Point Locking

Table 2/2

Katalognummer	Hurtigforsendelse
21630-521	Nej
21630-522	Nej
21630-523	Nej
21630-524	Nej
21630-525	Nej
21630-526	Nej
21630-527	Nej
21630-528	Nej
21630-529	Nej
21630-530	Nej
21630-531	Nej
21630-532	Nej

YDERLIGERE PRODUKTOPLYSNINGER

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE