

Varistar Server Cabinet, RAL 9003, Side-by-Side



Server rack for high static load requirements, completely assembled and grounded including side by side kits powder coated in white.

CERTIFICERINGER



FUNKTIONER

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different servers possible

Server cabinet with perforated doors, airflow rate 78 %

RAL 9003 (white)

SPECIFIKATIONER

Table 1/3

Katalognummer	Type	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
12130-275	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-276	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-285	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White

Katalognummer	Type	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
12130-286	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-279	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-280	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-289	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-290	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-283	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-284	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-293	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White
12130-294	Side-by-Side	Stål	Stål	Signal White	RAL 9003	Signal White

Table 2/3

Katalognummer	Cladding Color Code	Rack Height	Højde	Bredde	Dybde	Static Load
12130-275	RAL 9003	42U	2000mm	600mm	1000mm	1600kg
12130-276	RAL 9003	42U	2000mm	800mm	1000mm	1600kg
12130-285	RAL 9003	42U	2000mm	600mm	1200mm	1600kg
12130-286	RAL 9003	42U	2000mm	800mm	1200mm	1600kg
12130-279	RAL 9003	47U	2200mm	600mm	1000mm	1600kg
12130-280	RAL 9003	47U	2200mm	800mm	1000mm	1600kg
12130-289	RAL 9003	47U	2200mm	600mm	1200mm	1600kg

Katalognummer	Cladding Color Code	Rack Height	Højde	Bredde	Dybde	Static Load
12130-290	RAL 9003	47U	2200mm	800mm	1200mm	1600kg
12130-283	RAL 9003	52U	2450mm	600mm	1000mm	1600kg
12130-284	RAL 9003	52U	2450mm	800mm	1000mm	1600kg
12130-293	RAL 9003	52U	2450mm	600mm	1200mm	1600kg
12130-294	RAL 9003	52U	2450mm	800mm	1200mm	1600kg

Table 3/3

Katalognummer	Hurtigforsendelse
12130-275	Nej
12130-276	Nej
12130-285	Nej
12130-286	Nej
12130-279	Nej
12130-280	Nej
12130-289	Nej
12130-290	Nej
12130-283	Nej
12130-284	Nej
12130-293	Nej
12130-294	Nej

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE