

Schwenkrahmen für schwere Lasten



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

MERKMALE

Oberfläche aus lichtgrauem Strukturlack (RAL 7035) aus Polyesterpulver.

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Spring-loaded pivot post makes installation easy

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

Mounting holes accommodate either English or metric cage nuts, which are ordered separately

Swing-Out Rack Frame assemblies are supplied with mounting supports

Hinges that provide 170-degree rotation are optional

SPEZIFIKATIONEN

Dicke: 2.66mm
Farbe: Hellgrau
Oberfläche: Pulverbeschichtet
Farbcode: RAL 7035

Table 1/1

Katalognummer	Material	Passend für Rahmenbreite	Rack-Einheiten	Schnelles Schiff
PSF76	Baustahl	600mm	10U	No
PSF146	Baustahl	600mm	25U	No
PSF148	Baustahl	800mm	25U	No
PSF78	Baustahl	800mm	10U	No
PSF168	Baustahl	800mm	30U	No
PSF186	Baustahl	600mm	34U	No
PSF188	Baustahl	800mm	34U	No
PSF206	Baustahl	600mm	39U	No
PSF77	Baustahl	700mm	10U	No
PSF207	Baustahl	700mm	39U	No
PSF208	Baustahl	800mm	39U	No
PSF226	Baustahl	600mm	43U	No
PSF227	Baustahl	700mm	43U	No
PSF228	Baustahl	800mm	43U	No
PSF166	Baustahl	600mm	30U	No

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE