

Universal Busbar Supports, EUBS



This busbar support, EUBS, is available for one, two, or three bars up to 120 x 10 mm. The support can be mounted either at the top or bottom of the enclosure. It is available off the shelf and tested according to IEC 61439. This support is required when a high level of mounting flexibility is required.

MERKMALE

Description: Busbar support up to 4500A to be mounted horizontally or vertically. Mounts directly to the enclosure frame or with help of CLPF profiles. Available in one/two/three bars per phase for bar thickness 10 mm, and width from 30 to 120 mm.

Working temperature: -40°C up to 130°C.

Material: Reinforced polyamide and steel. Halogen free.

Delivery: Busbar support with mounting material.

SPEZIFIKATIONEN

Table 1/1						
Katalognummer	Stromschienendicke	Stromschienen pro Phase	Stromschienenbreite	Material	Oberfläche	Farbe
EUBS310TN	10mm min	3Ph min	30 – 125mm	Stahl, Polyamid	Beschichtet	Schwarz
EUBS110TN	10mm min	1Ph min	30 – 125mm	Stahl, Polyamid	Beschichtet	Schwarz
EUBS210TN	10mm min	2Ph min	30 – 125mm	Stahl, Polyamid	Beschichtet	Schwarz

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE