

Varistar CP Seismic Base/Plinth, 103H 800W 600D

Energieversorger

KATALOGNUMMER

21630-115

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

EIGENSCHAFTEN

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

PRODUKTMERKMALE

Product Type: Cabinet/Rack Base

Product Family: Varistar CP

Type: Base Plinth

Werkstoff: Stahl

Farbe: Black Grey

Farbcode: RAL 7021

Höhe: 103 mm

Breite: 800 mm

Tiefe: 800 mm

Complies With: IEC 61587-1; IEC 61587-2

Static Load: 400 N

Works With: Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE