

# EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

## Energieversorger

Rear horizontal rail for backplane mounting with insulation strip



## ZERTIFIZIERUNGEN

---



## EIGENSCHAFTEN

---

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

## SPEZIFIKATIONEN

---

Table 1/3

Katalognummer	Rack Height	Tiefe	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-161	3 U	175 mm	1	Backplane	160 mm	Textile
24563-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile
24563-461	6 U	175 mm	1	Backplane	160 mm	Textile
24563-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Handle Included	Montage	Konform mit	EMC Shielding	Product Type
24563-161	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-162	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-163	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-164	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-461	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-462	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis
24563-463	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis

Katalognummer	Shock and Vibration Tolerance	HandleIncluded	Montage	Konform mit	EMC Shielding	Product Type
24563-464	5 g (force)	Nein	Rack	IEC 60297-3-103	Nein	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Statische Last
24563-161	84 HP	15 kgf
24563-162	84 HP	15 kgf
24563-163	84 HP	15 kgf
24563-164	84 HP	15 kgf
24563-461	84 HP	15 kgf
24563-462	84 HP	15 kgf
24563-463	84 HP	15 kgf
24563-464	84 HP	15 kgf

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**