

Front Panel, Anodized, Unshielded, Screw Assembly

Energieversorger

Anodized front panel, unshielded version, Al, 2.5 mm.



ZERTIFIZIERUNGEN



EIGENSCHAFTEN

Partial width front panel, Al, 2.5 mm

Al, anodized

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish
30807-416	2 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-494	3 U	42 HP	1	Screw-on Front	Anodized	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish
30807-506	3 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-596	4 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-764	6 U	42 HP	1	Screw-on Front	Anodized	Anodized
30807-771	6 U	63 HP	1	Screw-on Front	Anodized	Anodized
30807-776	6 U	84 HP	1	Screw-on Front	Anodized	Anodized
30808-067	3 U	63 HP	1	Screw-on Front	Anodized	Anodized
30810-432	3 U	2 HP	5	Screw-on Front	Anodized	Anodized
30818-741	6 U	2 HP	5	Screw-on Front	Anodized	Conductive
30807-481	3 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-482	3 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-483	3 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-484	3 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-485	3 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-487	3 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-496	3 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-501	3 U	14 HP	5	Screw-on Front	Anodized	Anodized
30807-508	3 U	3 HP	5	Screw-on Front	Anodized	Anodized
30807-509	3 U	7 HP	5	Screw-on Front	Anodized	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montage	Front Finish	Rear Finish
30807-510	3 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-778	6 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-777	6 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-752	6 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-753	6 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-755	6 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-757	6 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-758	6 U	14 HP	5	Screw-on Front	Anodized	Conductive
30807-766	6 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-779	6 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-780	6 U	16 HP	5	Screw-on Front	Anodized	Anodized
30807-833	6 U	7 HP		Screw-on Front	Anodized	Anodized

Table 2/3

Katalognummer	Treated Edges	Konform mit	EMC Shielding	Höhe	Material	Product Type
30807-416	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	84 mm	Aluminium	Frontplatte
30807-494	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-506	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte

Katalognummer	Treated Edges	Konform mit	EMC Shielding	Höhe	Material	Product Type
30807-596	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	172.9 mm	Aluminium	Frontplatte
30807-764	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-771	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-776	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30808-067	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30810-432	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30818-741	Nein	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-481	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-482	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-483	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-484	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-485	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-487	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-496	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte

Katalognummer	Treated Edges	Konform mit	EMC Shielding	Höhe	Material	Product Type
30807-501	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-508	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-509	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-510	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	128.4 mm	Aluminium	Frontplatte
30807-778	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-777	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-752	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-753	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-755	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-757	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-758	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-766	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-779	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte
30807-780	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte

Katalognummer	Treated Edges	Konform mit	EMC Shielding	Höhe	Material	Product Type
30807-833	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nein	261.8 mm	Aluminium	Frontplatte

Table 3/3

Katalognummer	Typ	Breite	Zertifizierungen
30807-416	Front Panel without Handle	426.4 mm	RoHS
30807-494	Front Panel without Handle	213 mm	RoHS
30807-506	Front Panel without Handle	426.4 mm	RoHS
30807-596	Front Panel without Handle	426.4 mm	
30807-764	Front Panel without Handle	213 mm	RoHS
30807-771	Front Panel without Handle	319.7 mm	RoHS
30807-776	Front Panel without Handle	426.4 mm	RoHS
30808-067	Front Panel without Handle	319.7 mm	RoHS
30810-432	Front Panel without Handle	9.8 mm	RoHS
30818-741	Front Panel without Handle	9.8 mm	RoHS
30807-481	Front Panel without Handle	20 mm	RoHS
30807-482	Front Panel without Handle	30.1 mm	RoHS
30807-483	Front Panel without Handle	50.5 mm	RoHS
30807-484	Front Panel without Handle	40.3 mm	RoHS
30807-485	Front Panel without Handle	60.6 mm	RoHS

Katalognummer	Typ	Breite	Zertifizierungen
30807-487	Front Panel without Handle	106.3 mm	RoHS
30807-496	Front Panel without Handle	141.9 mm	RoHS
30807-501	Front Panel without Handle	70.8 mm	RoHS
30807-508	Front Panel without Handle	14.9 mm	RoHS
30807-509	Front Panel without Handle	35.2 mm	RoHS
30807-510	Front Panel without Handle	25 mm	RoHS
30807-778	Front Panel without Handle	20 mm	RoHS
30807-777	Front Panel without Handle	25 mm	RoHS
30807-752	Front Panel without Handle	30.1 mm	RoHS
30807-753	Front Panel without Handle	50.5 mm	RoHS
30807-755	Front Panel without Handle	60.6 mm	RoHS
30807-757	Front Panel without Handle	106.3 mm	RoHS
30807-758	Front Panel without Handle	70.8 mm	RoHS
30807-766	Front Panel without Handle	141.9 mm	RoHS
30807-779	Front Panel without Handle	40.3 mm	RoHS
30807-780	Front Panel without Handle	80.9 mm	RoHS
30807-833	Front Panel without Handle	35.2 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE